

FLOOR BOXES

FOR WOOD FRAME AND
CONCRETE CONSTRUCTION

ORDERING GUIDE

A COMPLETE
SOLUTION FOR
POWER, DATA & AV



Concrete Floor Boxes

For floors on ground
level or above



Poke-Through Floor Box

For floors above
ground level



Wood Frame Floor Boxes

Ideal for homes,
conference rooms,
auditoriums, stages,
hospitality, and more



Pop-Up Floor Boxes

Ideal for office
buildings, work-from-
home setups, desks,
conference rooms,
and more

FOR USE WITH ALL TYPES OF FLOORING INCLUDING WOOD,
TILE, VINYL, TERRAZZO, CARPET, AND CONCRETE.



Concrete Floor Boxes – PVC

- Elevation screws offer up to 3" of adjustment before installation
- Bulls-eye leveling cover ensures proper installation and protects during concrete pour
- Leveling ring allows for adjustment up to 3/4" after installation
- Low voltage divider has pre-scored, built-in measurements
- Solid brass flip-lid cover plates with double hinged design allows doors to open 180 degrees



SYSTEM

Description	Cat. No
Concrete Floor Box System, Gray (Includes reducers, dividers, and yellow leveling cover)	FBBOX-GY
Concrete Floor Box Leveling Ring (required)	FBLEV-GY

COVERS AND PLATES

Description	Nickel Cat. No	Black Cat. No	Brass Cat. No
1 Decora Flip Lid & 1 Data Cap Plate	FBC1F-N	FBC1F-E	FBC1F-B
2 Decora Flip Lids Plate	FBC2F-N	FBC2F-E	FBC2F-B
1 Screw Cap (Single Receptacle or Furniture Feed) & 2 Data Caps Plate Cap Diameters: Screw Cap, Ø 0.50", Ø 1.25" & Ø 1.50" (NPS)	FBC1S-N	FBC1S-E	FBC1S-B
2 Screw Caps (Duplex Receptacle) & 1 Data Cap Plate Cap Diameters: Screw Cap, Ø 0.50" & (2) Ø 1.25" (NPS)	FBC1X-N	FBC1X-E	FBC1X-B

ACCESSORIES

Description	Cat. No
Low Voltage Divider, Gray	FBDIV-GY
Power Conduit Reducers, Gray	FBRPW-GY
Data Conduit Reducers, Gray	FBRDT-GY
'Y' Conduit Adapter, Gray	FBYAD-GY
2-Port Decora Recessed Data Strap, Ivory	FB2DE-I
2-Port Duplex Recessed Data Strap, Ivory	FB2DU-I



Concrete Floor Boxes – Recessed Metallic Kits

- Floor box houses power and data below the floor for recessed plugging
- Stainless steel cover plates completely flush to floor; flip lids hidden while-in-use
- Rotating flange adjusts to finished floor height
- Black plastic sleeve covers 6" stamped steel floor box column



4" ROUND RECESSED OPENING, 6" HEIGHT

Description	Cat. No
Includes Leviton 16342-GY 20 Amp Decora Plus Receptacle, Industrial Grade, Self-Grounding	FBID1
Includes 2 NEMA 5-20R Power Outlets and 4 Data Ports	FBI24
Includes 4 NEMA 5-20R Power Outlets and 4 Data Ports	FBI44



ORDERING INFO ON THE GO!

Scan the QR codes for product info in the palm of your hand.



[LEVITON.COM/
FLOORBOXES](http://LEVITON.COM/FLOORBOXES)

LOOKING FOR MORE?

Visit leviton.com/floorboxes for product videos, features, benefits and ordering information.

Concrete Floor Boxes – Stamped Steel

- Once the stamped steel floor box is buried and cured in concrete, the tile ring and plates can be installed flush to the finished floor
- Each stamped steel floor box includes screws to height-adjust for thicker concrete slab floors
- Includes a concrete cover, leveling/height-adjusting screws and various sized conduit entries



PLATE MOUNTS:
FLUSH



SYSTEM			
Description	1-Gang Cat. No	2-Gang Cat. No	3-Gang Cat. No
Rectangle Deep Floor Box	FBDR1	FBDR2	FBDR3
Round Deep Floor Box	FBDC1	—	—
Rectangle Shallow Floor Box	FBHR1	FBHR2	FBHR3
FRAMES			
Description	1-Gang Cat. No	2-Gang Cat. No	3-Gang Cat. No
Brass Frames (Only needed for Rectangle Floor Boxes)	FBRM1	FBRM2	FBRM3
COVERS			
Description	Cat. No		
Rectangle Flip Lid 1 Door Duplex	FBCR1		
Round Flip Lid 1 Door Duplex	FBCR2		
Rectangle Flip Lid 1 Door Decora	FBCR3		
Round Flip Lid 1 Door Decora	FBCR4		

Poke-Through Floor Boxes

- Industry-exclusive self-leveling: two-piece construction levels device up to 4-degrees
- Industry-exclusive adjustable anchoring clips ease removal for inspections, adjustments and repairs
- Intumescent fire block & insulation provide 2+ hours of fire-rating
- Pre-installed gaskets & ground wire speed installation
- Industry-exclusive door-in-door cover design hides flip lids and maintains flush, clean appearance even when in use



PLATE MOUNTS:
FLANGED



SYSTEM				
Description	Cat. No			
5" Poke-Through Device	PT500			
COVERS AND PLATES				
Description	Gray Cat. No	Nickel Cat. No	Black Cat. No	Brass Cat. No
Pre-Wired Door-in-Door Floor Cover	PT544-2GY	PT544-2N	PT544-2E	PT544-2B
2-Gang Decora Door-in-Door Floor Cover	PT526-GY	PT526-N	PT526-E	PT526-B
2-Gang Decora Flip Lid Floor Cover	PTC2F-GY	PTC2F-N	PTC2F-E	PTC2F-B
2-Gang Duplex Flip Lid Floor Cover	PTC2X-GY	PTC2X-N	PTC2X-E	PTC2X-B
Furniture Feed Floor Cover - Cap Diameters : Ø .75", Ø 1.50" NPS	PT5FF-GY	PT5FF-N	PT5FF-E	PT5FF-B
Abandonment Floor Plate	PT5AB-GY	PT5AB-N	PT5AB-E	PT5AB-B
ACCESSORIES				
Description	Cat. No			
2-Port Decora Recessed Data Strap, Ivory	FB2DE-I			
2-Port Duplex Recessed Data Strap, Ivory	FB2DU-I			

Wood Frame Floor Boxes

- Plate gaskets on all, and rubber O-rings on rectangular covers, combine to seal out moisture and air-borne particles
- Meet or exceed UL514A requirements including the Scrub Water Test and comply with Section 4.3.8 of the Americans with Disabilities Act specifying accessible design
- Devices with tamper-resistant receptacles satisfy National Electrical Code® 2020 Article 406.12 requirements



25251-TFN



35249-TFB

PLATE MOUNTS:
FLANGED



RECTANGULAR FLOOR BOX KITS (RECEPTACLE INCLUDED)

Description	Tamper-Resistant	Cover Style	Color	1-Gang, 15 Amp Cat. No	1-Gang, 20 Amp Cat. No	2-Gang, 15 Amp Cat. No	2-Gang, 20 Amp Cat. No
Single Receptacle Floor Box Assembly	TR	Rectangle	Brass	5249-TFB	5349-TFB	—	—
Duplex Receptacle Floor Box Assembly	TR	Rectangle	Nickel	25249-TFN	25349-TFN	35249-TFN	35349-TFN
Duplex Receptacle Floor Box Assembly	TR	Rectangle	Brass	25249-TFB	25349-TFB	35249-TFB	35349-TFB
Duplex Receptacle Floor Box Assembly (includes 1 QuickPort Insert)	TR	Rectangle	Nickel	—	—	35249-TLN	35349-TLN
Duplex Receptacle Floor Box Assembly (includes 1 QuickPort Insert)	TR	Rectangle	Brass	—	—	35249-TLB	35349-TLB
Duplex Receptacle Floor Box Assembly	Non-TR	Rectangle	Nickel	25249-SBA	—	—	—
Duplex Receptacle Floor Box Assembly	Non-TR	Rectangle	Brass	25249-FBA	25349-FBA	—	—

ROUND FLOOR BOX KITS (RECEPTACLE INCLUDED)

Duplex Receptacle Floor Box Assembly	TR	Round	Nickel	25251-TFN	—	—	—
Duplex Receptacle Floor Box Assembly	TR	Round	Brass	25251-TFB	—	—	—
Decora Receptacle Floor Box Assembly	TR	Round	Nickel	25251-TDN	—	—	—
Decora Receptacle Floor Box Assembly	TR	Round	Brass	25251-TDB	—	—	—

ROUND BLANK FLOOR BOX KITS (RECEPTACLE NOT INCLUDED)

Description	Cover Style	Color	Cat. No
Blank Floor Box Assembly	Round	Nickel	25251-DN
Blank Floor Box Assembly	Round	Brass	25251-DB

REPLACEMENT PARTS FOR WOOD FRAME FLOOR BOXES

Description	Cat. No
Single Receptacle Replacement Cap & Gasket (for use with 5249-TFB & 5349-TFB)	5249-CAP
Duplex Receptacle Replacement Cap & Gasket (for use with 25249-FBA, 25249-TFB, 25349-FBA, 25349-TFB, 35249-TFB, 35349-TFB, 35249-TLB, 35349-TLB)	25249-CAP

Pop-Up Floor Box Receptacles

- Pre-wired terminal block for easy wiring access and installation
- Low profile, stylish metal cover recesses into the floor when not in use, reducing above floor height to ¼ inch



PLATE MOUNTS:
FLANGED



COVERS

Description	Brushed Nickel Cat. No	Bronze Cat. No	Black Cat. No	Brass Cat. No
Pop-Up Floor Box with 15A USB Charger Tamper-Resistant Receptacle	PFUS1-BN	PFUS1-BZ	PFUS1-MB	PFUS1-BR
Pop-Up Floor Box with 20A USB Charger Tamper-Resistant Receptacle	PFUS2-BN	PFUS2-BZ	PFUS2-MB	PFUS2-BR
Pop-Up Floor Box with 15A Self-Test GFCI Tamper-Resistant Receptacle	PFGF1-BN	PFGF1-BZ	PFGF1-MB	PFGF1-BR
Pop-Up Floor Box with 20A Self-Test GFCI Tamper-Resistant Receptacle	PFGF2-BN	PFGF2-BZ	PFGF2-MB	PFGF2-BR
Pop-Up Floor Box with 15A Tamper-Resistant Receptacle	PFTR1-BN	PFTR1-BZ	PFTR1-MB	PFTR1-BR
Pop-Up Floor Box with 20A Tamper-Resistant Receptacle	PFTR2-BN	PFTR2-BZ	PFTR2-MB	PFTR2-BR
Pop-Up Floor Box with 3-Port QuickPort	PFQP3-BN	PFQP3-BZ	PFQP3-MB	PFQP3-BR

Visit our Website at:

leviton.com/floorboxes

email: commercial@leviton.com

Leviton Manufacturing Co., Inc.

201 N Service Rd, Melville, NY 11747

Telephone: 1-800-323-8920 • FAX: 1-800-832-9538

Tech Line: 1-800-824-3005 (M-F 8AM-10PM; Sat 9AM-7PM; Sun 9AM-5PM)

© 2024 Leviton Manufacturing Co., Inc. All rights reserved.

Q-1524 080724