



THE FUTURE IS ON®

LEVITON®



Energy Industry Solutions

LINE CARD



ENERGY INDUSTRY SOLUTIONS

Rhino-Hide® 49 Series Single Pole High Amperage Devices

- Up to 1135 A, 1000 V
- Insulators molded of high performance TPV
- Ideal for installations on both new and existing silicon-controlled rectifiers (SCRs), generator stations, and new oil or gas rigs



Rhino-Hide® Single Pole Cam Devices

- Up to 690 A, 600 V
- Insulators molded of high performance TPV
- Slit and cam male contact design compensates for wear
- Specific models are flame-resistant for MSHA compliance



Portable GFCIs

- 15 and 20 A, 120 V
- Rainproof, outdoor rated GFCI module
- Complies with NEC and OSHA regulations for construction sites
- Automatic and manual reset versions



Portable Outlet Boxes & Covers

- Single- and two-gang, feed-thru and pendant style boxes
- Flip-lid covers are rated NEMA Type 3R
- Resistant to heat, harsh chemicals and impacts



Wetguard® Watertight Devices

- 15-30 A, 125-600 V
- NEMA and Non-NEMA configurations
- UL/Fed. Spec./CSA/NOM
- Plugs, connectors, inlets, outlets, covers and accessories
- Industry leading lifetime warranty
- IP66, IP67, IP69K* and NEMA 4, 4X, 6, 6P

*Plugs and connectors need caps attached in order to achieve IP69K rating



Black & White® Extra Heavy-Duty Plugs & Connectors

- 15-50 A, 125-600 V
- NEMA and Non-NEMA configurations
- UL/Fed.Spec./CSA/NOM
- Corrosion-resistant devices available
- Industry leading lifetime warranty



LEV Series IEC 60309 Pin & Sleeve Devices

- 30 A & 60 A North American Configurations
- IP66, IP67, IP68 and IP69K Rated
- Improved safety and productivity with Inform™ Technology



Rhino-Hide® Rough Service Devices

- 15-20 A, 125-250 V
- Straight blade and locking plugs, connectors and receptacles
- IP66, IP67, IP68, IP69K and NEMA 3R, 4, 4X, 6, 6P, 12, 13
- Industry leading lifetime warranty



EV Series Electric Vehicle Charging Stations

- 32, 48 or 80 Amp
- Level 2: SAE J1772™ Compatible
- Restrict access with optional RFID
- Compatible with the My Leviton app
- Available with 4G and management software capabilities



Industrial Grade Weatherproof Covers

- For use with 15, 20, 30 and 50 A devices
- IP64 and NEMA 3R rated
- Provisions for OSHA compliant lockout/tagout
- Pre-mounted gasket and stay open feature simplify installation



Visit our Website at:
leviton.com/energy
email: industrial@leviton.com

Leviton Manufacturing Co., Inc.
201 N Service Rd, Melville, NY 11747
Telephone: 1-800-323-8920 • FAX: 1-800-832-9538
Tech Line: 1-800-824-3005 (M-F 8AM-10PM; Sat 9AM-7PM; Sun 9AM-5PM)
© 2024 Leviton Manufacturing Co., Inc. All rights reserved. Q-743G 122723