

Commercial QUICKPORT™ UTP Patch Panels (empty)


	Flat						Angled				
	Standard Density					High Density	Standard Density				High Density
	49255-H24	49255-L24	49255-H48 49255-48N	49255-L48	49455-48B	49255-Q48 49255-V48	49256-H24	49256-L24	49256-H48	49256-L48	49256-D48
RU	1RU		2RU			1RU	1RU		2RU		1RU
Ports	24		48				24		48		
Labeling	Silk-Screened Blocks	Mag Lens	Silk-Screened Blocks	Mag Lens	Silk-Screened Numbering		Silk-Screened Blocks	Mag Lens	Silk-Screened Blocks	Mag Lens	Silk-Screened Numbering
Cable Mgt.	Included with black panels (except 49355-H24 and 49355-H48) White panel cable mgt. sold separately (P/N 49005-CMB)					Sold Separately (P/N 49005-DMB)	Sold Separately (P/N 49006-AMB)				
Color	Black White (49255-W24)	Black	Black White (49255-W48)	Black			Black White (49256-W4L)	Black White (49256-W4M)	Black White (49256-W8L)	Black White (49256-W8M)	Black
Country of Origin	Please Contact Customer Service			Please Contact Customer Service	China	Please Contact Customer Service	Please Contact Customer Service		Please Contact Customer Service		China
Jack Installation Location	Rear-Loading			Front-Loading	Rear-Loading		Rear-Loading				



49455-48B



49255-H24



49255-W48



49256-L48



49256-D48

Commercial QUICKPORT™ Shielded Patch Panels (empty)

		e2XHD	Shielded					
		e2XHD Flat and Angled	Flat Standard Density		Flat High Density	Angled Standard Density		
		E2X1^S48	4S255-S24	4S255-S48	4S255-48N	4S255-D48	4S256-S24	4S256-S48
RU		1RU	1RU	2RU		1RU		2RU
Ports		48	24	48			24	48
Labeling		Silk-Screened Numbering	Silk-Screened Blocks			Silk-Screened Numbering	Silk-Screened Blocks	
Cable Mgt.		Sold Separately E2XHD-CMD (angled panels) E2XHD-CMB (flat panels)	Included with Black panels White panel cable mgt. sold separately (P/N 49005-CMB)			Sold Separately (P/N 49005-DMB)	Sold Separately (P/N 49006-AMB)	
Color		Black	Black White (4S255-WS4)	Black White (4S255-WS8)	Black	Black White (4S255-W48)	Black White (4S256-WS4)	Black White (4S256-WS8)
Country of Origin		Taiwan	Please Contact Customer Service		Taiwan		Please Contact Customer Service	Please Contact Customer Service

^ Flat/angled available



Commercial Patch Panels

	Cat 5e		Cat 6					Cat 6A			
	Flat	Flat QUICKPORT™ Panel Kit ^	Flat		Angled		Flat QUICKPORT Panel Kit ^	Flat	Angled	Flat QUICKPORT Panel Kit ^	
	5G596-U**	5G270-U**	69586-U**	69586-C48	69586-L**	69587-U**	69587-L**	69270-U**	6A586-U**	6A587-U**	6910G-U**
RU	1RU (24 Port) 2RU (48 Port)	1RU (24 Port) 2RU (48 Port)	1RU (12, 24 Port) 2RU (48 Port) 4RU (96 Port)	2RU	1RU (24 Port) 2RU (48 Port)	1RU (24 Port) 2RU (48 Port)	1RU (24 Port) 2RU (48 Port)	1RU (24 Port) 2RU (48 Port)	1RU (24 Port) 2RU (48 Port)		
Ports	24, 48		12, 24, 48, 96	48	24, 48				24, 48		
Labeling	Paper	Silk-Screened Blocks	Paper		Mag Lens	Paper	Mag Lens	Silk-Screened Blocks	Mag Lens		Silk-Screened Blocks
PoE Rating	Up to 60W		Up to 100W					Up to 100W			
Cable Mgt.	Included		Included with black panels White panel cable mgt. sold separately (P/N 49005-CMB)		Sold Separately (P/N 49006-AMB)		Included		Included	Sold Separately (P/N 49006-AMB)	Included
Country of Origin	USA		USA					USA			
Color	Black		Black White (69586-W**)	Black					Black		

** 24-ports, 1RU (24), 48-Ports, 2RU (48)



5G596-U24



5G596-U48



69586-W48



6910G-U24

