

P Series

Surge Protective Device

Designed for **RESIDENTIAL AND LIGHT COMMERCIAL APPLICATIONS**,

the P Series provides protection in single, split or three phase configurations.

Features

- Maximum Surge Current Rating 25kA per Mode, 50kA per Phase
- UL 1449 Listed



- 200kA SCCR
- NEMA 4X





Product Specifications

General Specifications			
Maximum Surge Current Rating	25kA per Mode, 50kA per Phase		
UL 1449 Type Designation	Type 1		
UL 1449 Nominal Discharge Current Rating (I _n)	20kA		
UL 1449 Short Circuit Current Rating (SCCR)	200kA		
Design Specifications			
Custom MOV design for High Energy Handling in IEEE Category C locations			
Thermally Protected MOVs	Thermally Protected MOVs		
External Parallel Connected for Mounting nex	External Parallel Connected for Mounting next to Electrical Gear		
Multi-mode protection			
Diagnostic & Status Monitoring Specifications			
LED Protection Status Monitoring			
Audible Alarm			
Form C Dry Contacts, 240V, 2A			
Phase Loss Monitoring	Phase Loss Monitoring		
Stacked MOV design for High Energy Handling	Stacked MOV design for High Energy Handling		
Enclosure			
Polycarbonate			
NEMA 4X			
3/4 inch NPT Side Mount Nipple			
Filtering			
NO			

Ρl	nysical Specifications	
	Humidity Range	0-95% non-condensing
	Operating Frequency	50-60Hz
	Operating Temperature	-31°F (-35°C) to 185°F (+85°C)
	Typical Connection	#12 AWG Type TEW

	.)					
Ul	UL 1449 Performance Data					
	System Voltage	Voltag L-N	ge Protect L-G	ion Rating N-G	(VPR)	Maximum Continuous Operating Voltage (MCOV)
	120/240 VAC/CA SPLIT PHASE	700V	1200V	600V	1200V	180V/360V*
	208Y/120 VAC/CA 3 PHASE WYE	600V	1000V	600V	1000V	150V/300V*
	480Y/277 VAC/CA 3 PHASE WYE	1200V	2500V	1000V	2000V	350V/700V*

^{*}Second voltage refers to L-L rating

Standards Compliance & Certifications

UL 1449 5th Edition: 2021, cULus, (UL File: VZCA.E317603), UL 96A Compliant, ANSI/IEEE C62.41.1-2002, C62.41.2-2002, C62.45-2002, NEC Article 285
ISO 9001:2014 Quality Management System, ISO 17025:2007 Laboratory Certification (UL DAP Program) Compliance with RoHS, REACH & California Prop 65
100% Quality Tested prior to shipping, Country of Origin: Greece


Ordering Information

P2120-B	120/240 VAC/CA, SPLIT PHASE
P3120-YB	208Y/120 VAC/CA, THREE PHASE WYE
P3277-YB	480Y/277 VAC/CA, THREE PHASE WYE

Accessories for Flush Mount Applications


PSURG-FLG P SERIES FLUSH MOUNT FLANGE - POLYCARBONATE

Wiring Configurations





Architectural Drawings (Dimensions)

P SERIES




	82.5mm	
	SURGE PROTECTIVE LEVITON.	
	GREEN LIGHTS: ON = Protection Operational OFF = Loss of Power/Protection L3 O	3.25" 82.5mm
	P2120-B TYPE 1, 120/240 VAC/CA, SPLIT PHASE IN RATNIC 2004; SCCR 20016A NEMA 4X RATED CC 2016A	
3/4" - 14 NPT Threads		





Size and Mechanical Specifications		
Dimensions	5.02" x 2.93" x 3.25"	
Enclosure Type	Polycarbonate NEMA 4X	
Installation Type	Indoor / Outdoor	

FLUSH MOUNT FLANGE



052924



Visit our Website at: www.leviton.com/surge email: commercial@leviton.com Q-1504

Leviton Manufacturing Co., Inc.

201 N Service Rd, Melville, NY 11747

Telephone: 1-800-323-8920 • FAX: 1-800-832-9538

Tech Line: 1-800-824-3005 (M-F 8AM-10PM; Sat 9AM-7PM; Sun 9AM-5PM)

© 2024 Leviton Manufacturing Co., Inc. All rights reserved.

