

Berk-Tek LANmark-C542 Cat 5e High Flex Shielded TPE

Berk-Tek LANmark Industrial Heavy-Duty Ethernet Cables enable the expansion and integration of Ethernet into the Industrial environment. With over 50 years of manufacturing expertise, you can be sure these Industrial Cables will perform both mechanically and electrically. With its 600V AWM design, durable TPE jacket, cold-bend performance, and resistance to oil, weld spatter, and sunlight, this cable is suitable for the most demanding, continuous-motion, industrial applications. This product has both a foil shield and a braid to protect against low- and high-frequency noise on the factory floor. Additionally, the stranded conductors also help maintain performance in a high-vibration environment. It is rated CMR and CMX Outdoor, so it easily transitions from indoor to outdoor environments and is also suitable for cable tray installations.

DESCRIPTION

Construction

24 AWG stranded tinned copper wire insulated with HDPE. Two insulated conductors twisted together to form a pair and four such pairs to form the basic unit, surrounded by polypropylene tape. Aluminum/polyester tape shield and 38 AWG braid of 75% optical coverage contained within a TPE jacket.

Related Standards

Low Voltage - EU Directive 2014/35/EU, CE Approved

RoHS - EU Directive 2011/65/EU


PoE+ - Type 2 (802.3at)

Agency Ratings

Description	Method	
Listed Type	UL1685	CMR
Listed Type	UL444	CMX Outdoor
Oil Resistance	UL1277 11.2	II (75°C)
Sunlight Resistance	UL444 7.22	Yes (720 hrs)

Attributes

Description	Method	
AWM Style	UL758	2463 (600V, 80°C)
Flex Life	C-Track, 4" radius	> 35 million cycles
Flex Life	Torsion (+/- 270°)	> 3 million cycles
Installation Pull Tension (Max):		
Bend Radius: > 3 inch	Internal	40 lbs.
Bend Radius: > 1.2 inch	TIA 568-C.0	25 lbs.
Abrasion	UL2556 7.10	50 cycles/1.5 lb. load



EtherNet/IP™
ODVA

CC-Link IE
Field Compliant

STANDARDS

International ISO/IEC 11801;
ODVA EtherNet/IP Compliant

National ANSI/TIA-568.2-D;
UL 444

CHARACTERISTICS

Construction characteristics

Conductor material	24 AWG Stranded Tinned Copper (7/32)
Insulation	HDPE
Jacket Material	TPE
Braid	Tinned copper - 75% optical coverage
Shielding	Aluminum/Polyester
Core Tape	Foamed polypropylene

Dimensional characteristics

Insulated conductor diameter (Nominal)	0.046 in
Average jacket thickness	0.033 in
Minimum jacket thickness at any point	0.026 in
Cable diameter (Nominal)	0.3 in
Nominal cable weight	46 lb/kft

Electrical characteristics

Mutual capacitance	5.6 nF/100m max.
DC Resistance (max.)	9.38 Ohm/100m
DC resistance unbalance (max.)	5 %
Nominal velocity of propagation	66 %
Maximum pair to ground unbalance	330 pF/100m






Transmission characteristics


Skew (max.)	45 ns/100m
Insertion loss de-rating factor	1.2

Usage characteristics

Minimum Bending Radius - Install	1.2 in
Recommended installation temperature range	-20 .. 80 °C
Recommended operating temperature range	-40 .. 80 °C
Recommended storage temperature range	-40 .. 80 °C
Maximum cable length	83 m
Cold Bend	-40 °C
Weld spatter resistance	Yes

PRODUCT LIST

Part Number	Description	Length per reel [ft]	Colour
 11099188	LANmark-C542 Cat 5e High Flex Shielded TPE	1000.0	Teal
 11100607	LANmark-C542 Cat 5e High Flex Shielded TPE	1000.0	Red
 11101961	LANmark-C542 Cat 5e High Flex Shielded TPE	1000.0	Black
 11100606	LANmark-C542 Cat 5e High Flex Shielded TPE	1000.0	Blue
 11100866	LANmark-C542 Cat 5e High Flex Shielded TPE	1000.0	Yellow

 = Make to order,  = In stock

LANMARK-C542 - TECHNICAL INFORMATION

Electrical Characteristics		
Parameter	Frequency	Equation
RL (dB)	1-10 MHz	$20+5*\text{Log}(F)$
	10-20 MHz	25
	20-100 MHz	$25-7*\text{Log}(F/20)$
Insertion Loss (dB/100m)	1-100 MHz	$(1.967*\sqrt{F}+0.023*F+0.050/\sqrt{F})*1.2$
NEXT (dB)	1-100 MHz	$35.3-15*\text{Log}(F/100)$
PS-NEXT (dB)	1-100 MHz	$32.3-15*\text{Log}(F/100)$
ACR (dB/100m)	1-100 MHz	NEXT - Insertion Loss
PS-ACR	1-100 MHz	PS-NEXT - Insertion Loss
ACRF (dB)	1-100 MHz	$23.8-20*\text{Log}(F/100)$
PSACRF (dB)	1-100 MHz	$20.8-20*\text{Log}(F/100)$
Propagation Delay	1-100 MHz	$534+(36/\sqrt{F})$
Max Transfer Impedance (mΩm)	1; 10; 30; 100 MHz	50; 100; 200; 1000
Min Coupling Attenuation (dB/100m)	30-100 MHz	55
ODVA EtherNet/IP™ Compliant		Category 5e

Transmission Characteristics		
Description		
ISO/IEC 11801		Category 5
ANSI/TIA-568.2-D		Category 5e
Coupling Attenuation	IEC 61156-5	Type II
Transfer Impedance	IEC 61156-5	Grade 2

Color Code		
Pair-1	White/Blue	Blue
Pair-2	White/Orange	Orange
Pair-3	White/Green	Green
Pair-4	White/Brown	Brown